

Overview

The PD charger + battery example is a simple demonstration based on the MCUXpresso SDK PD stack. The application simulate battery product (for example: laptop), it prints the battery percent continually. The demo works as DRP. When connect, the board can be source or sink.

System Requirement

Hardware requirements

- One or two Type-C shield board
- One or two 9V DC power suppliers
- Type-C Cable
- One or two hardwares (Tower module/base board, and so on) for a specific device, for example: lpcxpresso54114 board
- Personal Computer

Software requirements

- The project files are in:
<MCUXpresso_SDK_Install>/boards/<board>/usb_examples/usb_pd_charger_battery/<rtos>/<toolchain>.

Note

The <rtos> is Bare Metal or FreeRTOS OS.

- Terminal tool.

Getting Started

Hardware Settings

For detailed instructions, see the appropriate board User's Guide.

Note

Set the hardware jumpers (Tower system/base module) to default settings.

Prepare the example

1. Download the program to the target board.
2. Power on Type-C shield board then power on development board.

Run the example

1. Connect the board to one charger or another shield board + development board (download this program too) with Type-C cable.
2. Connect the OpenSDA USB port to the PC and open terminal.
3. If running as source after connect.
 - If battery is (30%, 100%]: source caps are high power (5V/9V).
 - If battery is (0%, 30%]: source caps are low power (only 5V).
 - If partner request power role swap: accept.
 - prefer to work as sink.
 - get partner source cap, and judge whether to swap (if partner is external powered and satisfy self request).
 - * if get partner source cap fail, retry one more time.

- * if can swap, then start power role swap.
- * if cannot swap or get source cap fail. still work as source.
- do power role swap.
 - * if fail, re-try one more time, if still fail, still work as source.
 - * if success, please reference to sink description.
- battery will decrease (if battery decrease to [0%, 20%]):
 - get partner source cap, and judge whether to swap (source cap satisfy self request).
 - * if get partner source cap fail, retry one more time.
 - * if can swap, then start power role swap.
 - * if cannot swap or get source cap fail, send low power source caps.
 - do power role swap.
 - * if fail, re-try one more time, if still fail send low power source caps.
 - * if success, please reference to sink description.
 - if swap fail, after send low power source caps to trigger source capabilities change.
 - * retry swap with interval 10s.
 - if battery decrease to 5%:
 - * stop provide vbus.
 - * set Try.SNK

4. Running as sink after connect.

- when connect:
 - if battery is less than 100%: request high power (9V).
 - if battery is 100%: request low power (5V).
- when battery increase to 100%, request low power (5V).
- If partner request power role swap
 - if battery is (30%, 100%]: accept.
 - if battery is [0%, 30%]: reject.
- when battery increase to (30%, 100%]:
 - update self source caps as high power.